





DIGITAL ELECTRONIC CONTROL UNIT FOR OPEN-LOOP SINGLE SOLENOID PROPORTIONAL VALVES SERIES 10

OPERATING PRINCIPLE



PLUG VERSION




TECHNICAL CHARACTERISTICS

Power supply	V DC	10 ÷ 30 - ripple included	
Required power	W	min 20 - max 40 (see paragraph 2.1)	
Output current	mA	min 800 - max 2600 (see paragraph 1)	
Power supply electrical protections		overload over 33V polarity inversion	
Output electrical protections		short-circuit	
Analogue electrical protections		up to 30 V DC	
Available reference signals (selectable from the jumper)	0 ÷ 10 V 0 ÷ 5 V 4 ÷ 20 mA	input impedance 100 k Ω input impedance 100 k Ω input impedance max 500 Ω	
Connector type		EN 175301-803 (ex DIN 43650)	
Electromagnetic compatibility (EMC): - EMISSIONS IEC EN 61000-6-4 - IMMUNITY IEC EN 61000-6-2		according to 2014/30/EU standards (see paragraph 5 - NOTE 1)	
Protection to atmospheric agents (IEC EN 60529)		IP 65/67	
Operating temperature range	°C	-20 / +70	
Mass	kg	0,10	

89 120/117 ED 1/4



1 - IDENTIFICATION CODE



The EDC-1 connector is a digital amplifier controlling open loop proportional valves. The unit supplies a variable current proportionally to the reference signal and independently of temperature variations or load impedance, with a resolution of 1% on 2600 mA (the full scale value).

The PWM stage on the solenoid power supply makes it possible to reduce the valve hysteresis thus optimising control precision. The connector is customizable with different maximum current sizes and switching frequencies (PWM), optimized according to the valve to be controlled.

Setting is possible by buttons and display inside the case, or by a notebook with software EDCPC/10 via RS232 (see par. 6.2).

2 - FUNCTIONAL SPECIFICATIONS

2.1 - Electric power supply

The connector requires a power supply of $10 \div 30 \text{ V DC}$ (terminals 1 and 2).

NOTE: The value of the power supply voltage on the connector must be higher than the rated working voltage of the solenoid to be controlled.

The power supply voltage must be rectified and filtered, with maximum admissible ripple within the above voltage range.

The power required by the connector depends on the power supply voltage and on the maximum value of the supplied current (it is determined by the card version). In general a conservative value of the required power can be considered as the product of V x I.

Example: a connector with maximum current = 800 mA and power supply voltage of 24 V DC requires a power of about 20 W.

In case of a card with maximum current = 1600 mA and power supply voltage of 24 V DC the used power is equal to 38.5 W.

2.2 - Electrical protection


The connector is protected against overvoltage and polarity inversion.

A protection against any short circuit is foreseen on the output.

2.3 - Reference signal

The connector accepts voltage reference signals with $0 \div 10 \text{ V}$ and $0 \div 5 \text{ V}$, in $4 \div 20 \text{ mA}$ current, from an external generator (PLC, CNC) or external potentiometer.

See paragraph 7 for electric connections referring to the different connector versions.



3 - SIGNALS

3.1 - POWER ON (Power supply)

The lit display indicate that the connector is ON and with +24V DC.

4 - ADJUSTMENTS

There are two way adjustments: variables view and parameters editing. The first one enables the real-time monitoring of the control values, for both required and read current, on both channels. The second mode enables the view and the editing of the operating parameters.

4.1 - Variables overview

The card is switched on at the variables view mode, and it shows the first variable value, that is the U1 parameter (reference signal).

Pushing button (1) the current to solenoid (C1 parameter) is displayed. By means of (1) key, the different variables can be selected.

By briefly pressing the keys, switching from a variable to the next, thevariable name appears for approximately one second.

89 120/117 ED 2/4



Variables that can be selected are:

U1: Reference signal:

0 + 10 V 0 + 5 V

4 ÷ 20 mA (displayed as 2 ÷ 10)

C1: current required according to the applied

reference signal, expressed in ampere, ranging

between 0 and 2.6 A

All the mentioned parameters can be viewed on the two digits display, located on the connector front panel.

The selected value has to be read as follows (example for EDC-15*/10E* card):

REFERENCE		DISPLAY U1		DISPLAY C1	
	(V)	(mA)	(V)		(Ampere)
	0	4	0.0	2.0	4 [] _(mA)
	5	12	5.0	6.0	13 _(A)
	10	20	10.	10.	5e (v)

4.2 - Parameters editing

To access the parameter editing, press the key (2) for at least 3 seconds.

The first parameter displayed is G1. To modify it, press the key (1) for two seconds, until the display starts blinking. Use the key (2) to increase the value and the key (1) to decrease it. To save the new value, press both the keys. The display stops blinking.

Pressing the key (2) again is possible to scroll all the parameters. To modify another parameter, repeat the steps above-mentioned for the G1 parameter.

The parameters that can be selected are:

G1: "I Max" current, expressed in milliampere.

It sets the maximum current to the solenoid, when the reference signal is at the maximum value of ± 10 V (or 20 mA). It is used to limit the maximum value of the hydraulic size controlled by the valve.

Default value = Imax

Range = $50 \div 100\%$ of Imax

o1: "I Min" current, expressed in milliampere.

It sets the offset current to the solenoid, when the reference signal exceeds the limit of 0,1 V (or 0,1 mA). It is used to null the insensitiveness area of the valve (dead band).

Default value = 0%

Range = $0 \div 50\%$ of Imax

u1: "Ramp Up" increasing ramp time, expressed in seconds.

It sets the current increasing time, for a variation from 0 to 100% of the input reference.

It is used to slow down the valve response time in case of a sudden variation of the reference signal.

Default value = 00 sec.

Range = $00 \div 50$ sec.

d1: "Ramp Dn" decreasing ramp time, expressed in seconds.

It sets the current decreasing time, for a variation from 100% to 0 of the input reference. It is used to slow down the valve response time in case of a sudden variation of the reference signal.

Default value = 00 sec.


Range = $00 \div 50$ sec.

Fr: PWM frequency, in Hertz.

It sets the PWM frequency, which is the pulsating frequency of the control current. The PWM decreasing improves the valve accuracy, decreasing the regulation stability. The PWM increase improves the regulation stability, causing a higher hysteresis.

Default value = PWM (according to version card)

Range = 50 ÷ 500 Hz



4.3 - Error signal

EE: breakdown cable error on 4 ÷ 20 mA signal (threshold 3 mA). Reset the alarm turning off the +24 V DC.

89 120/117 ED 3/4



5 - INSTALLATION

The electronic unit with connector shape mounting is suitable for assembly directly on the 4-pin coil connection of the proportional valve to be energized.

NOTE 1: To observe EMC requirements it's important that the control unit electrical connection is compliant with the wiring diagram of chapter 7.

As a general rule, the valve and the electronic unit connection wires must be kept as far as possible from interference sources (e.g. power wires, electrical motors, inverters and electrical switches).

A complete protection of the connection wires can be requested in environments with critical electromagnetic interferences.

6 - START UP, CONTROL SETTINGS AND SIGNAL MEASUREMENT

6.1 - Set up

Settings can be changed by either acting on the (1) and (2) keys located on the card front panel, or using the EDCPC/10 software kit with converter and related cable.


6.2 - EDCPC/10 Software (code 3898301001)

The relevant hardware and software kit (to be ordered separately) allows to read the values and to set the connector easily.


It is necessary to connect the EDC-1 to the PC through a special cable (flat cable). The socket is located inside the EDC-1 connector, behind the protective cover.

The EDCPC/10 software is compliant with Microsoft Windows 2000, XP, Vista and Win 7 operating systems.

7 - WIRING DIAGRAM



8 - OVERALL AND MOUNTING DIMENSIONS





DUPLOMATIC MS S.p.A.

via M. Re Depaolini 24 • 20015 PARABIAGO (MI) • ITALY tel. +39 0331.895.111 • www.duplomatic.com • e-mail: sales.exp@duplomatic.com